

17 Section 17
Conveyor Components



Conveyor Parts, Conveyor Components, Adjusting Rods, Support Heads, Cross Blocks, Support Bases

Conveyor components are used to construct equipment that moves products or materials from one place to another, such as assembly lines, and packaging and bottling machinery. Our line of conveyor parts includes adjusting rods and the components needed to attach and mount them, such as cross blocks, clamps, and brackets.

Clamping knobs and heads are used to make adjustments to the motion on a conveying system. Roller guides are used to construct the tracks upon which materials glide from place to place. Standing systems are constructed with rods or tubing using support heads, mounting brackets, bases such as bipods and tripods, and tube expander fittings. To accommodate turning elements, we offer a variety of flange and pillow block bearings.

Special modifications available:
- lengths

Conveyor parts and conveyor accessories are also referred to as:
plastic clamps, support brackets, side brackets, plastic bases, tripod bases, and bi-pod bases

The items below are just a sampling of the complete line of AVE conveyor components we have available. Call us with your requirements or for more information!

Download a pdf of the entire Ave conveyor components catalog by clicking on the cover to the right (29 MB). --> (Please note: pages F1 - F25 products are not available for purchase.)



Download a [printable pdf of this section index page](#)
More about our [machining and packaging capacities](#)
Read posts about [conveyor components](#) on the J.W. Winco blog

In This Section:

[Cross Blocks](#)
[Photocell Clamps](#)
[Adjusting Rods](#)
[Guide Rod and Rail Clamps](#)

[Side Brackets](#)
[Clamping Knobs and Heads](#)
[Roller Guides](#)
[Support Heads and Mounting Brackets](#)

[Connection Joints and Support Bases](#)
[Tube Expander Fittings](#)
[Flange and Pillow Block Bearings](#)

Cross Blocks



[WN 600](#)
[Cross Blocks for](#)
[Square or Round](#)
[Tubes](#)

[AN 700](#)
[Cross Blocks -](#)
[Base Style](#)


Photocell Clamps



[AN 605](#)
[Clamps for](#)
[Photocell](#)

[AN 600](#)
[Clamps for](#)
[Photocell or](#)
[Reflector](#)

Adjusting Rods



[WN 760](#)
[Adjusting Rods,](#)
[Blank Type](#)

[WN 761](#)
[Adjusting Rods,](#)
[with Groove](#)

[WN 762](#)
[Adjusting Rods,](#)
[Tapped and](#)
[Milled Flats Type](#)

[WN 764](#)
[Adjusting Rods,](#)
[Milled Flats Type](#)

Guide Rod and Rail Clamps



[AN 505](#)
[Single Clamps](#)
[with Rod for](#)
[Conical Side](#)
[Guide Rails](#)

[AN 500](#)
[Single Clamps for](#)
[Conical Side](#)
[Guide Rails](#)

[AN 520](#)
[Plastic Double](#)
[Guide Rod](#)
[Clamps](#)

[AN 522](#)
[Plastic Double](#)
[Guide Rail](#)
[Clamps](#)

[AN 524](#)
[Plastic Double](#)
[Guide Rail](#)
[Clamps](#)

Side Brackets



[AN 400](#)
[Side Brackets](#)



[AN 410](#)
[Adjustable Side Brackets with 4-Prong Knob](#)



[AN 420](#)
[Adjustable Side Brackets with 4-Prong Knob](#)



[AN 425](#)
[Adjustable Side Brackets with 4-Prong Knob](#)

Clamping Knobs and Heads



[AN 5662](#)
[Plastic Star Knob with Nickel Plated Brass Hexagon Boss, Tapped Type](#)



[AN 5662](#)
[Plastic Star Knob with Nickel Plated Brass Hexagon Boss, Stud Type](#)



[AN 5670](#)
[Plastic Clamping Heads With Threaded Eye Bolt Top Side](#)



[AN 5671](#)
[Plastic Clamping Heads With Threaded Eye Bolt Bottom Side](#)



[AN 5672](#)
[Nickel-Plated Brass or Stainless Steel Clamping Heads for Clamping Knob or Screw](#)

Roller Guides



[GN 753](#)
[Guide Rollers](#)



[AN 813](#)
[Roller Guide Adjusting Rods](#)



[AN 815](#)
[45 mm Roller Guides](#)



[AN 817](#)
[70 mm Roller Guides](#)



[AN 819](#)
[96 mm Roller Guides](#)



[AN 821](#)
[120 mm Roller Guides](#)

Support Heads and Mounting Brackets



[AN 310](#)
[Support Heads Square Base, for 38 mm Tubing](#)



[AN 315](#)
[Support Heads Square Base, for 20 mm Tubing](#)



[AN 300](#)
[Support Heads, Rectangular Base](#)



[AN 305](#)
[Support Heads, Square Base](#)



[AN 210](#)
[Side Mount Brackets](#)



[AN 200](#)
[Side Mount Brackets](#)



[AN 205](#)
[Side Mount Brackets](#)

Connection Joints and Support Bases



[AN 250](#)
[Plastic Connection Joints](#)



[AN 260](#)
[Stainless Steel Connection Joints](#)



[AN 115](#)
[Bipod Support Bases](#)



[AN 120](#)
[Bipod Support Bases with Round Connection Joint](#)



[AN 100](#)
[Tripod Support Bases](#)

Tube Expander Fittings



[AN 350](#)
[Tube Expander Fittings for 25 mm OD x 1.5 mm Wall Thickness Square Tubing](#)



[AN 351](#)
[Tube Expander Fittings for 30 mm OD x 2 mm Wall Thickness Square Tubing](#)



[AN 352](#)
[Tube Expander Fittings for 20 mm OD x 1.5 mm Wall Thickness Round Tubing](#)



[AN 354](#)
[Tube Expander Fittings for 30 mm OD x 1.5 mm Wall Thickness Round Tubing](#)



[AN 355](#)
[Angled Connection Joints for 38 mm OD x 1.5 mm Wall Thickness Round Tubing](#)

Flange and Pillow Block Bearings



[AN 7870](#)
[Plastic and Steel Square Flange Bearing](#)



[AN 7870.1](#)
[Stainless Steel Square Flange Bearing](#)



[AN 7872](#)
[Plastic and Steel Oval Flange Bearing](#)



[AN 7872.1](#)
[Stainless Steel Oval Flange Bearing](#)



[AN 7876](#)
[Plastic and Steel Mini-Oval Flange Bearing](#)



[AN 7874](#)
[Plastic and Steel Pillow Block Flange Bearing](#)



[AN 7874.1](#)
[Stainless Steel Pillow Block Flange Bearing](#)