



7 Section 7 Leveling Elements

Leveling Mounts, Leveling Feet, and Threaded Tube Ends and Inserts



Leveling elements are used to provide a level, stable base for machinery or equipment, one that limits tipping, vibration, wear and noise. We offer an excellent selection of leveling feet to accommodate every application. Our steel and stainless steel leveling mounts are available in tapped and stud types, with or without pads. Versions with articulated bases, lag bolt lugs, special sanitary features, and simple, economical design are included. We have designs appropriate for all sizes and weight requirements.

Our plastic base levelers have steel or stainless steel studs or tapped sockets, and are offered with or without articulation and lag holes. Again, the selection accommodates a large range of size and weight requirements.

Also in this section are tube ends for use in modifying standard tubing for use with leveling feet, as well as our vibration/isolation and shock absorption mounts.

In This Section:

- [Threaded Tube Ends, Tube Inserts and Mounting Plates](#)
- [Vibration / Isolation and Shock Absorption Mounts](#)
- [Metal Base Leveling Mounts](#)
- [Plastic Base Leveling Mounts](#)
- [Miscellaneous Levelers](#)

Special modifications available:

- stud configurations
- threaded stud lengths
- thread sizes
- base sizes and configurations
- mounting holes

Leveling elements are also referred to as:

leveling feet, leveling mounts, leveler bolts, antivibration pads, antivibration mounts, Level-It mounts, Level-It pads, machinery mounts, levelers, leveling devices, Glide-Rite mounts, Glide-Rite pads, machine feet, articulating feet, machinery foot, leveling foot, and swivel mounts

Download a [printable pdf of this section index page](#)
More about our [machining and packaging capacities](#)
Read posts about [leveling elements](#) on the J.W. Winco blog

Threaded Tube Ends, Tube Inserts and Mounting Plates



SN 992
Inch Size Threaded
Tube Ends for
Round Tubes



SN 993
Inch Size Threaded
Tube Ends for
Square Tubes



EN 458
Inch Size Plastic
Threaded Round
Tube Ends



EN 448S
Inch and Metric
Size Plastic
Threaded Square
Tube Ends



EN 448R
Inch and Metric
Size Plastic
Threaded Round
Tube Ends



EN 348
Metric Size Plastic
Threaded Square
Tube Ends



GN 992
Metric Size
Aluminum
Threaded Tube
Inserts



GN 992.5
Metric Size
Stainless Steel
Threaded Tube
Inserts



GN 349
Metric Size Steel
Threaded
Mounting Plates
for Leveling
Mounts

Vibration / Isolation and Shock Absorption Mounts



GN 351.1 /
GN 351.2 /
GN 351.3
Inch Vibration
Isolation Mounts
with Steel
Components,
Cylindrical Type



GN 351
Metric Vibration
Isolation Mounts
with Steel
Components,
Cylindrical Type



GN 451.1 /
GN 451.2 /
GN 451.3
Inch
Vibration Isolation
Mounts with
Stainless Steel
Components,
Cylindrical Type



GN 451
Metric Vibration
Isolation Mounts
with Stainless Steel
Components,
Cylindrical Type



GN 352.1 /
GN 352.2
Inch Vibration /
Shock Absorption
Mounts with Steel
Components,
Cylindrical Type



GN 352
Metric Vibration /
Shock Absorption
Mounts with Steel
Components,
Cylindrical Type



GN 452.1 /
GN 452.2
Inch
Vibration / Shock
Absorption Mounts
with Stainless Steel
Components,
Cylindrical Type



GN 452
Metric Vibration /
Shock Absorption
Mounts with
Stainless Steel
Components,
Cylindrical Type



GN 353.1 /
GN 353.2
Inch
Vibration / Shock
Absorption Mounts
with Steel
Components,
Conical Type



GN 353
Metric
Vibration / Shock
Absorption Mounts
with Steel
Components,
Conical Type



GN 453.1 /
GN 453.2
Inch
Vibration / Shock
Absorption Mounts
with Stainless Steel
Components,
Conical Type



GN 453
Metric
Vibration / Shock
Absorption Mounts
with Stainless Steel
Components,
Conical Type



GN 253
NEW
Inch and Metric
Vibration / Shock
Absorption
Mounts with Steel
Components,
Conical Type

Download the informational sheet about our anti-vibration mounts

Lose those bad vibes.
Vibration mounts. Shock absorbers. Leveling feet. And more.

- High quality, economical, standard components for shock absorbing, cushioning, vibration isolation and shock absorption.
- Available in steel, stainless steel, aluminum, plastic and brass.
- Customized designs available for special applications.
- ISO 9001:2008 certified manufacturing process.

Application Areas:
• Industrial machinery
• Agricultural machinery
• Material handling equipment
• Construction equipment
• Marine equipment
• Food processing equipment

Contact us today to discuss your application requirements.

J.W. WINCO, INC. www.jwwinco.com



GN 254
NEW
Inch and Metric
Vibration / Shock
Absorption Mounts
with Stainless
Steel Components,
Conical Type

Metal Base Leveling Mounts



SNSM
Inch and Metric
Snap-Lock Non-
Skid Leveling
Mounts



TNSM
Inch and Metric
Snap-Lock Non-
Skid Leveling
Mounts



GN 342.2
NEW
Metric Size Stud
Type Steel
Vibration
Dampening
Leveling Mounts



GN 342.1
NEW
Metric Size
Tapped Type Steel
Vibration
Dampening
Leveling Mounts



GN 343.2
Metric Size Stud
Type Steel Base
Leveling Mounts



GN 343.1
Metric Size
Tapped Type Steel
Base Leveling
Mounts



GN 343.6
Metric Size
Stainless Steel
Leveling Mounts
with
Technopolymer
Plastic Base



GN 343.5
Metric Size
Stainless Steel
Leveling Mounts
with
Technopolymer
Plastic Base



LPST
Inch Size
"LEVEL-IT"
Leveling Mounts



MLPST
Metric Size
"LEVEL-IT"
Leveling Mounts



LPSO
Inch Size
"LEVEL-IT"
Leveling Mounts



MLPSO
Metric Size
"LEVEL-IT"
Leveling Mounts



AVM
Inch Size "ANTI-
VIBE" Leveling
Mounts



MAVM
Metric Size
"ANTI-VIBE"
Leveling Mounts



AVLM
Inch Size "ANTI-
VIBE" Leveling
Mounts



MAVLM
Metric Size
"ANTI-VIBE"
Leveling Mounts



MM 100
Inch Size Mighty
Mount™
Heavy Duty
Vibration Mounts



LP 100
Inch Size Zinc
Plated Steel Low
Profile Leveling
Mounts



LP 100.1
Inch Size Stainless
Steel Low Profile
Leveling Mounts



GN 21
Metric Size
Stainless Steel
Leveling Feet with
Turned Base,
without Mounting
Bores



GN 23
Metric Size
Stainless Steel
Leveling Feet with
Turned Base, with
Mounting Bores



GN 40
Inch and Metric
Size Steel Leveling
Feet



GN 40
Inch and Metric
Size Steel Leveling
Feet



GN 41
Inch and Metric
Size Stainless Steel
Leveling Feet



GN 41
Inch and Metric
Size Stainless
Steel Leveling
Feet



GN 41
Metric Size
Stainless Steel
Leveling Feet



GN 41
Metric Size
Stainless Steel
Leveling Feet



GN 41
Metric Size
Stainless Steel
Leveling Feet for
Sanitary
Applications



GN 42
Inch and Metric
Size Steel Leveling
Feet with Fixing
Lug



GN 42
Inch and Metric
Size Steel
Leveling Feet with
Fixing Lug



GN 43
Inch and Metric
Size Stainless Steel
Leveling Feet with
Fixing Lug



GN 43
Inch and Metric
Size Stainless Steel
Leveling Feet with
Fixing Lug



GN 43
Metric Size
Stainless Steel
Leveling Feet with
Fixing Lug



GN 43
Metric Size
Stainless Steel
Leveling Feet with
Fixing Lug



GN 43
Metric Size
Stainless Steel
Leveling Feet with
Fixing Lug



GN 30
Inch and Metric
Size Steel Leveling
Mounts with
Rubber Pad



GN 30
Inch and Metric
Size Steel Leveling
Mounts with
Rubber Pad



GN 31
Inch and Metric
Size Stainless Steel
Leveling Mounts
with Rubber Pad



GN 31
Inch and Metric
Size Stainless Steel
Leveling Mounts
with Rubber Pad



GN 31
Metric Size
Stainless Steel
Leveling Mounts
with Rubber Pad



GN 31
Metric Size
Stainless Steel
Leveling Mounts
with Rubber Pad



GN 31
Metric Size
Stainless Steel
Leveling Feet for
Sanitary
Applications,
Black Rubber Pad



GN 31
Metric Size
Stainless Steel
Leveling Feet for
Sanitary
Applications,
White Rubber Pad



GN 32
Inch and Metric
Size Steel Leveling
Mounts with Lag
Bolt Lug



GN 32
Inch and Metric
Size Steel
Leveling Mounts
with Lag Bolt Lug



GN 33
Inch and Metric
Size Stainless Steel
Leveling Mounts
with Lag Bolt Lug



GN 33
Inch and Metric
Size Stainless Steel
Leveling Mounts
with Lag Bolt Lug



GN 33
Metric Size
Stainless Steel
Leveling Mounts
with Lag Bolt Lug



GN 33
Metric Size
Stainless Steel
Leveling Mounts
with Lag Bolt Lug



GN 33
Metric Size
Stainless Steel
Leveling Feet for
Sanitary
Applications, with
Lag Bolt Lug



GN 339
Metric Size Steel
Leveling Mounts



GN 339
NEW
Metric Size Steel
Leveling Mounts



GN 6311.4
Metric Size Steel
Leveling Feet with
or without Plastic
Base Cap



IIG
Inch Size Steel
"Glide-Rite"
Industrial Glides
with Nylon Pad



MIG
Metric Size Steel
"Glide-Rite"
Industrial Glides
with Nylon Pad



IIG-EL
Inch Size Steel
"Glide-Rite"
Industrial Glides
with Elastomer
Pad



MIG-EL
Metric Size Steel
"Glide-Rite"
Industrial Glides
with Elastomer
Pad



EN 248
Metric Size, Steel
Stud Type
Leveling Feet With
Vibration
Dampening Pad



GN 148
Metric Size,
Threaded Insert
Type Leveling Feet
With Vibration
Dampening Pad



GN 148.2
Metric Size,
Rubber Pads for
GN 148 Leveling
Feet

Plastic Base Leveling Mounts



GN 343.4
Metric Size Steel
Leveling Mounts
with
Technopolymer
Plastic Base



GN 343.3
Metric Size Steel
Leveling Mounts
with
Technopolymer
Plastic Base



GN 343.8
Metric Size
Stainless Steel
Leveling Mounts
with
Technopolymer
Plastic Base



GN 343.7
Metric Size
Stainless Steel
Leveling Mounts
with
Technopolymer
Plastic Base



GN 638 /
GN 638-NI
Steel and Stainless
Steel Grub Screw
and Thrust Pad
Assemblies



PM 200
Inch and Metric
Size Steel
PolyMount
Leveling Mounts



WN 9000
Steel "NY-LEV"
Nylon Base
Mounts with Lag
Holes



WN 9000.1
Stainless Steel
"NY-LEV" Nylon
Base Mounts with
Lag Holes



WN 9100
Steel "NY-LEV"
Nylon Base
Mounts without
Lag Holes



WN 9100.1
Stainless Steel
"NY-LEV" Nylon
Base Mounts
without Lag Holes



EN 244
Metric Size Steel
Stud Type
Technopolymer
Plastic Base
Leveling Mounts



PM 500
Inch and Metric
Size Steel
PolyMount
Leveling Mounts



PM 500.1
Inch and Metric
Size Stainless Steel
PolyMount
Leveling Mounts



WN 9000
Inch and Metric
Steel "NY-LEV"
Nylon Base
Mounts with Lag
Holes



WN 9000.1
Inch and Metric
Stainless Steel
"NY-LEV" Nylon
Base Mounts with
Lag Holes



WN 9100
Inch and Metric
Steel "NY-LEV"
Nylon Base
Mounts without
Lag Holes



WN 9100.1
Inch and Metric
Stainless Steel
"NY-LEV" Nylon
Base Mounts
without Lag Holes



EN 839
NEW
Metric Size, Steel
Stud Type
Technopolymer
Plastic Base
Leveling Mount



EN 839.5
NEW
Metric Size,
Stainless Steel
Stud Type
Technopolymer
Plastic Base
Leveling Mount



PM 500
Inch Size Steel
PolyMount
Leveling Mounts



PM 500.1
Inch Size Stainless
Steel PolyMount
Leveling Mounts



PM 600
Inch Size Steel
Teardrop
PolyMount
Leveling Mounts



PM 600.1
Inch Size Stainless
Steel Teardrop
PolyMount
Leveling Mounts

Miscellaneous Levelers



SN 946
Inch Size Steel
Willi Glide
Leveling Mounts



SN 949
Inch Size Steel
Hex Leveler Bolts



SN 974
Inch Size Steel
Rattle Mounts

J.W. Winco, Inc. © 2017 | [Terms and Conditions](#) | [Privacy / Disclaimer](#) | [ISO 9001:2008](#) | 800-877-8351

Page updated 04/03/2017